





序号	名称	数量
1	底座	1
2	阳接触针	n
3	焊片	2



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



说明:

1. 产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;

2. 塑胶材料:LCP UL94V-0,颜色:本色;

3. 焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;

4. 接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;

5. 满足灼热丝温度850度.

6. 工作温度-40~+85°C




7. 额定电流:2A AC/DC

8. 额定电压:100V AC/DC

9. 接触阻抗:10mΩ Max.

10. 绝缘阻抗:1000MΩ Min.

11. 耐压:800V AC FOR 1 MINUTE



P/N	PIN	DIM A	DIM B	DIM C
JXT-HY2.0-2PWT	2	2.00	8.00	4.80
JXT-HY2.0-3PWT	3	4.00	10.00	6.80
JXT-HY2.0-4PWT	4	6.00	12.00	8.80
JXT-HY2.0-5PWT	5	8.00	14.00	10.80
JXT-HY2.0-6PWT	6	10.00	16.00	12.80
JXT-HY2.0-7PWT	7	12.00	18.00	14.80
JXT-HY2.0-8PWT	8	14.00	20.00	16.80
JXT-HY2.0-9PWT	9	16.00	22.00	18.80
JXT-HY2.0-10PWT	10	18.00	24.00	20.80
JXT-HY2.0-11PWT	11	20.00	26.00	22.80
JXT-HY2.0-12PWT	12	22.00	28.00	24.80
JXT-HY2.0-13PWT	13	24.00	30.00	26.80
JXT-HY2.0-14PWT	14	26.00	32.00	28.80
JXT-HY2.0-15PWT	15	28.00	34.00	30.80
JXT-HY2.0-16PWT	16	30.00	36.00	32.80
JXT-HY2.0-17PWT	17	32.00	38.00	34.80
JXT-HY2.0-18PWT	18	34.00	40.00	36.80
JXT-HY2.0-19PWT	19	36.00	42.00	38.80
JXT-HY2.0-20PWT	20	38.00	44.00	40.80

TOLERANCE

X.:±0.30

X':±5°

X.X:±0.25

X.X':±3°

X.XX:±0.20

X.XX':±1°

UNITS

mm

MATERILA

— — —

FINISH

— — —



深圳聚兴泰电子科技有限公司
Shenzhen Juxingtai Electronic Technology Co., Ltd

PART NO.

JXT-HY2.0-XPWT

DESIGN: Ethan

CHED: Olivia

APPD: Ava

TITLE:

PHB-SMT-AW

MANUFACTURE DWG

SCALE

SHEET

N:A 1/1