



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTE

1.SPECIFICATIONS

WITHSTANDING VOLTAGE: 500V AC

CURRENT RATING: 2AMP

INSULATION RESISTANCE: 1000MΩ MIN

CONTACT RESISTANCE: 20 mΩ MAX

TEMPERATURE RANGE: -55℃ ~ +85℃

2.MATERIAL

HOUSING: THERMOPLASTIC UL94V-0

CONTACT: BRASS

3.FINISH: SEE TABLE





Table:

PART NAME	Q'TY	Material
CONTACT	1	C2680R-H,NI 80U"
HOUSING	1	PBT+30%GF,BLACK
CONTACT	1	C2680R-H,GOLD FLASH
CONTACT	1	C2680R-H,GOLD 15U"
CONTACT	1	C2680R-H,GOLD 30U"
CONTACT	1	C2680R-H,半金镍0.4U"

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X:±0.30	±1	PART NO. 2.54-060-PT-B	TITLE: 2.54mm 开口短路帽		
.XX:±0.20			MANUFACTURE DWG		
.XXX:±0.10					
UNITS	mm	DESIGN: Ethan	 SCALE SHEET		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			