








P/N	PIN	$DIM\ A$	$DIM\ B$	$DIM\ C$
$JXT-HA2.54-2PWT$	2	2.50	9.90	5.90
$JXT-HA2.54-3PWT$	3	5.00	12.40	8.40
$JXT-HA2.54-4PWT$	4	7.50	14.90	10.90
$JXT-HA2.54-5PWT$	5	10.00	17.40	13.40
$JXT-HA2.54-6PWT$	6	12.50	19.90	15.90
$JXT-HA2.54-7PWT$	7	15.00	22.40	18.40
$JXT-HA2.54-8PWT$	8	17.50	24.90	20.90
$JXT-HA2.54-9PWT$	9	20.00	27.40	23.40
$JXT-HA2.54-10PWT$	10	22.50	29.90	25.90
$JXT-HA2.54-11PWT$	11	25.00	32.40	28.40
$JXT-HA2.54-12PWT$	12	27.50	34.90	30.90
$JXT-HA2.54-13PWT$	13	30.00	37.40	33.40
$JXT-HA2.54-14PWT$	14	32.50	39.90	35.90
$JXT-HA2.54-15PWT$	15	35.00	42.40	38.40
$JXT-HA2.54-16PWT$	16	37.50	44.90	40.90
$JXT-HA2.54-17PWT$	17	40.00	47.40	43.40
$JXT-HA2.54-18PWT$	18	42.50	49.90	45.90
$JXT-HA2.54-19PWT$	19	45.00	52.40	48.40
$JXT-HA2.54-20PWT$	20	47.50	54.90	50.90

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X'.':±5°	PART NO. JXT-HA2.54-XPWT	TITLE: HA-SMT-AW 带扣针座		
X.X:±0.25	X.X':±3°				
X.XX:±0.20	X.XX':±1°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG 		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			

1. 产品表面清洁, 无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料: LCP UL94V-0, 颜色: 本色;
3. 焊片: 黄铜, 镍底 30u"Min., 镀锡 50u"Min.;
4. 接触针: 黄铜, 镍底 30u"Min., 镀锡 50u"Min.;
5. 满足灼热丝温度 850 度.
6. 工作温度 -40~+85°C
7. 额定电流: 3A AC/DC
8. 额定电压: 250V AC/DC
9. 接触阻抗: 10mΩ Max.
10. 绝缘阻抗: 1000MΩ Min.
11. 耐电压: 1000V AC FOR 1 MINUTE