







说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:2A AC/DC
- 8.额定电压:100V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐电压:800V AC FOR 1 MINUTE



序号	名称	数量
1	基座	1
2	阳接触针	n
3	定位焊片	2

P/N	PIN	DIM A	DIM B	DIM C
JXT-PH2.0-2PLT	2	2.00	7.90	4.75
JXT-PH2.0-3PLT	3	4.00	9.90	6.75
JXT-PH2.0-4PLT	4	6.00	11.90	8.75
JXT-PH2.0-5PLT	5	8.00	13.90	10.75
JXT-PH2.0-6PLT	6	10.00	15.90	12.75
JXT-PH2.0-7PLT	7	12.00	17.90	14.75
JXT-PH2.0-8PLT	8	14.00	19.90	16.75
JXT-PH2.0-9PLT	9	16.00	21.90	18.75
JXT-PH2.0-10PLT	10	18.00	23.90	20.75
JXT-PH2.0-11PLT	11	20.00	25.90	22.75
JXT-PH2.0-12PLT	12	22.00	27.90	24.75
JXT-PH2.0-13PLT	13	24.00	29.90	26.75
JXT-PH2.0-14PLT	14	26.00	31.90	28.75
JXT-PH2.0-15PLT	15	28.00	33.90	30.75
JXT-PH2.0-16PLT	16	30.00	35.90	32.75
JXT-PH2.0-17PLT	17	32.00	37.90	34.75
JXT-PH2.0-18PLT	18	34.00	39.90	36.75
JXT-PH2.0-19PLT	19	36.00	41.90	38.75
JXT-PH2.0-20PLT	20	38.00	43.90	40.75

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±5°	PART NO. JXT-PH2.0-XPLT	TITLE: PH-SMT-A针座		
X.X:±0.25	X.X':±3°				
X.XX:±0.20	X.XX':±1°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 1/1