







说明:

1. 产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料:LCP UL94V-0,颜色:本色;
3. 焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
4. 接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
5. 满足灼热丝温度850度.
6. 工作温度-40~+85°C
7. 额定电流:2A AC/DC
8. 额定电压:100V AC/DC
9. 接触阻抗:10mΩ Max.
10. 绝缘阻抗:1000MΩ Min.
11. 耐电压:800V AC FOR 1 MINUTE

序号	名称	数量
1	基座	1
2	阳接触针	n
3	定位焊片	2



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



P/N	PIN	DIM A	DIM B	DIM C
JXT-PH2.0-2PWT	2	2.00	7.90	4.70
JXT-PH2.0-3PWT	3	4.00	9.90	6.70
JXT-PH2.0-4PWT	4	6.00	11.90	8.70
JXT-PH2.0-5PWT	5	8.00	13.90	10.70
JXT-PH2.0-6PWT	6	10.00	15.90	12.70
JXT-PH2.0-7PWT	7	12.00	17.90	14.70
JXT-PH2.0-8PWT	8	14.00	19.90	16.70
JXT-PH2.0-9PWT	9	16.00	21.90	18.70
JXT-PH2.0-10PWT	10	18.00	23.90	20.70
JXT-PH2.0-11PWT	11	20.00	25.90	22.70
JXT-PH2.0-12PWT	12	22.00	27.90	24.70
JXT-PH2.0-13PWT	13	24.00	29.90	26.70
JXT-PH2.0-14PWT	14	26.00	31.90	28.70
JXT-PH2.0-15PWT	15	28.00	33.90	30.70
JXT-PH2.0-16PWT	16	30.00	35.90	32.70
JXT-PH2.0-17PWT	17	32.00	37.90	34.70
JXT-PH2.0-18PWT	18	34.00	39.90	36.70
JXT-PH2.0-19PWT	19	36.00	41.90	38.70
JXT-PH2.0-20PWT	20	38.00	43.90	40.70

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.30	X':±5°	PART NO. JXT-PH2.0-XPWT	TITLE: PH-SMT-AW针座	
X.X:±0.25	X.X':±3°			
X.XX:±0.20	X.XX':±1°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olivia		
MATERILA	— — —	APPD: Ava	SCALE N:A	SHEET 1/1
FINISH	— — —			