










说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:0.7A AC/DC
- 8.额定电压:30V AC/DC
- 9.接触阻抗:30mΩ Max.
- 10.绝缘阻抗:100MΩ Min.
- 11.耐压:200V AC FOR 1 MINUTE



PCB Layout



P/N	PIN	DIM A	DIM B	DIM C	DIM D
JXT-0.8-2PWT	2	0.80	3.04	3.80	1.90
JXT-0.8-3PWT	3	1.60	3.84	4.60	2.70
JXT-0.8-4PWT	4	2.40	4.64	5.40	3.50
JXT-0.8-5PWT	5	3.20	5.44	6.20	4.30
JXT-0.8-6PWT	6	4.00	6.24	7.00	5.10
JXT-0.8-7PWT	7	4.80	7.04	7.80	5.90
JXT-0.8-8PWT	8	5.60	7.84	8.60	6.70
JXT-0.8-9PWT	9	6.40	8.64	9.40	7.50
JXT-0.8-10PWT	10	7.20	9.44	10.20	8.30
JXT-0.8-11PWT	11	8.00	10.24	11.00	9.10
JXT-0.8-12PWT	12	8.80	11.04	11.80	9.90
JXT-0.8-13PWT	13	9.60	11.84	12.60	10.70
JXT-0.8-14PWT	14	10.40	12.64	13.40	11.50
JXT-0.8-15PWT	15	11.20	13.44	14.20	12.30
JXT-0.8-16PWT	16	12.00	14.24	15.00	13.10
JXT-0.8-17PWT	17	12.80	15.04	15.80	13.90
JXT-0.8-18PWT	18	13.60	15.84	16.60	14.70
JXT-0.8-19PWT	19	14.40	16.64	17.40	15.50
JXT-0.8-20PWT	20	15.20	17.44	18.20	16.30

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±5°	PART NO. JXT-0.8-XPWT	TITLE: 0.8-NP贴片,卷装,亮锡,LCP		
X.X:±0.25	X.X':±3°		MANUFACTURE DWG		
X.XX:±0.20	X.XX':±1°	DESIGN: Ethan			
UNITS	mm	CHED: Olivia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —				
			SCALE N:A	SHEET 1/1	