





RoHS



NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance:  $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage: AC 500V 1Minute
- 4.Operating Force Range: 1000gf Max
- 5.Mechanical Life: 3,000 Cycles

|     |                |        |     |                 |              |
|-----|----------------|--------|-----|-----------------|--------------|
| (F) | Dust film      |        | 1   | Polyimide tape  |              |
| (E) | Terminal       |        | 12  | Phosphor bronze | Gold plating |
| (D) | Contact spring |        | 6   | Phosphor bronze | Gold plating |
| (C) | Handle         |        | 6   | PA46            | White        |
| (B) | Cover          |        | 1   | PPS             | Black        |
| (A) | Base           |        | 1   | PPS             | Black        |
| NO. | Name           | Number | Qty | Materil         | Remarks      |

YUANDI® Yuandi Electronics Co.,Ltd

|          |      |       |            |
|----------|------|-------|------------|
| design   | date | name  | DIP SWITCH |
| Review   | date | model | TP-06      |
| Approved | date |       |            |

Drawing number:

|        |        |          |                         |            |     |      |    |             |    |
|--------|--------|----------|-------------------------|------------|-----|------|----|-------------|----|
| modify | Review | Approved | Tolerance not specified | Proportion | 1:1 | unit | mm | gape number | A4 |
|--------|--------|----------|-------------------------|------------|-----|------|----|-------------|----|