






RoHS



NOTE:
1.Rating: 24V 25mA DC
2.Insulation Resistance: $\geq 100\text{ M}\Omega$
3.Withstand voltage: AC 500V 1Minute
4.Operating Force Range: 1000gf Max
5.Mechanical Life: 3,000 Cycles

(F)	Dust film		1	Polyimide tape	
(E)	Terminal		8	Phosphor bronze	Gold plating
(D)	Contact spring		4	Phosphor bronze	Gold plating
(C)	Handle		4	PA46	White
(B)	Cover		1	PPS	Black
(A)	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	DIP SWITCH
Review	date	model	TP-04
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved

angle	$\pm 2^\circ$
10~30	± 0.30
5~10	± 0.20
~ 5	± 0.10

Tolerance not specified