


P. C. B Layout

技术要求:

Technical requirement

一. 电气性能:

electrical performance

1-1. 额定电流: 3A AC DC.

rated current: 3A AC DC.

1-2. 接触电阻: $\leq 20\text{m}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

1-3. 绝缘电阻: $\geq 1000\text{M}\Omega$

Insulation resistance: $\geq 1000\text{M}\Omega$

1-4. 耐压: 550V AC/Minute

withstand voltage: 550V AC/Minute

二. 物理特性:

Physical characteristics

2-1.: 环境温度-55℃~105℃

environmental temperature:-55℃~105℃

2-2. 焊接温度: +240℃, 10s max

welding temperature:+240℃, 10s max

三. 材质:

Material

3-1. 塑胶: PA66(Black) UL94V-2

plastic: PA66(Black) UL94V-2

3-2. 插针: 黄铜

contact pin: Brass/Gold plated

未注明公差 Tolerance				Product Chain		4.2-1*NA实心针	
				Dwg No			
XX.	±0.40	XX.°	±2°	Drawer	Y.K	Scale	1:1
X.	±0.30	.XX°	±1°	Sign	Sun	Unit	MM
.X	±0.20			Approve	Sun		
.XX	±0.15						