



产品编号 : 1202530024

Product Description : Contrinex Inductive Sensor,  
M8 Housing, 6mm Operating Distance, Non-embeddable,  
NPN, NO, 2m 3-wire PVC Cable, 45mm Housing Length

系列号 : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric  
Sensors

工程编号 : DW-AD-511-M8



## 文件和资源

### 规格

[1202530024-000.pdf](#)

## 产物环境合规

### 合规

|                    |                                                  |
|--------------------|--------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                     |
| China RoHS         | per SJ/T 11365-2006                              |
| EU ELV             | Not Relevant                                     |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21                  |
| REACH SVHC         | Not Reviewed per D(2024)7663-DC<br>(21 Jan 2025) |
| EU RoHS            | Compliant with Exemption 6(c) per<br>EU 2015/863 |

### 合规声明

- EU RoHS
- REACH SVHC
- Low-Halogen

### 行业文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### 关注物质

- PFAS

### 欧盟 RoHS 合格证书

### 附加信息

产品详情

一般

|       |                                                                                                                                   |
|-------|-----------------------------------------------------------------------------------------------------------------------------------|
| 状态    | Not Recommended For New Design                                                                                                    |
| 类别    | Inductive Sensors                                                                                                                 |
| 系列    | 120253                                                                                                                            |
| 说明    | Contrinex Inductive Sensor, M8 Housing, 6mm Operating Distance, Non-embeddable, NPN, NO, 2m 3-wire PVC Cable, 45mm Housing Length |
| IP 等级 | IP67                                                                                                                              |
| 产品名称  | Contrinex                                                                                                                         |
| 类型    | Inductive                                                                                                                         |
| UPC   | 191130061945                                                                                                                      |

电气

|      |          |
|------|----------|
| 输出   | NO       |
| 极性   | NPN      |
| 交换频率 | ≤ 500 Hz |

物理

|          |                        |
|----------|------------------------|
| 连接       | Cable (PVC 2m, 3-wire) |
| 长度       | 45mm                   |
| 材料－外壳    | Chrome Plated Brass    |
| 材料 – 感应面 | PBTP (PPS)             |
| 安装方式     | Non-embeddable         |
| 工作距离     | 6mm                    |
| 输出       | NO                     |
| 传感器外壳尺寸  | M8                     |
| 运行温度范围   | -25° to +70° C         |