



产品编号 : [1202530438](#)

**Product Description :** Contrinex Inductive Sensor, M12 Housing, 8mm Operating Distance, Non-embeddable, NPN, NO, 4-pin M12 Connector, 45mm Housing Length

系列号 : 120253

**Status :** Not Recommended For New Design

**Product Category :** Inductive and Photoelectric Sensors

工程编号 : DW-AS-631-M12-120



## 文件和资源

### 规格

[1202530434-000.pdf](#)

## 产物环境合规

### 合规

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### 合规声明

- EU RoHS
- REACH SVHC
- Low-Halogen

### 行业文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### 关注物质

- PFAS

[欧盟 RoHS 合格证书](#)

## 附加信息

UKCA – Declaration of Conformity

CE – Declaration of Conformity

---

## 产品详情

### 一般

状态	Not Recommended For New Design
类别	Inductive Sensors
系列	120253
说明	Contrinex Inductive Sensor, M12 Housing, 8mm Operating Distance, Non-embeddable, NPN, NO, 4-pin M12 Connector, 45mm Housing Length
IP 等级	IP67
产品名称	Contrinex
类型	Inductive
UPC	191130067435

### 电气

输出	NO
极性	NPN
交换频率	≤ 1400 Hz

### 物理

连接	Connector (M12, 4-pin)
长度	45mm
材料—外壳	Nickel Plated Brass
材料 - 感应面	PBTP
安装方式	Non-embeddable
工作距离	8mm
输出	NO
传感器外壳尺寸	M12
运行温度范围	-25° to +70° C