



产品编号 : [1202530499](#)

Product Description : Contrinex Inductive Sensor,
3mm Diameter Short and Smooth Housing, 1mm
Operating Distance, Embeddable, PNP, NO, 2m 3-wire
PUR Cable, 12mm Housing Length

系列号 : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric
Sensors

工程编号 : DW-AD-623-03-960



文件和资源

规格

[1202530498-000.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

合规声明

- EU RoHS
- REACH SVHC
- Low-Halogen

行业文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

关注物质

- PFAS

欧盟 RoHS 合格证书

附加信息

产品详情

一般

状态	Not Recommended For New Design
类别	Inductive Sensors
系列	120253
说明	Contrinex Inductive Sensor, 3mm Diameter Short and Smooth Housing, 1mm Operating Distance, Embeddable, PNP, NO, 2m 3-wire PUR Cable, 12mm Housing Length
IP 等级	IP67
产品名称	Contrinex
类型	Inductive
UPC	191130068647

电气

输出	NO
极性	PNP
交换频率	≤ 8000 Hz

物理

连接	Cable (PUR 2m, 3-wire)
长度	12mm
材料－外壳	Stainless Steel
材料 – 感应面	POM
安装方式	Embeddable
工作距离	1mm
输出	NO
传感器外壳尺寸	3mm dia. (short and smooth)
运行温度范围	-25° to +70° C