

RoHS

REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		Jack	Larry	J.L.Y	2021-06-27


NOTE:

1.MATERIALS AND FINISHED
INSULATOR : LCP UL-94V0,
COVER:LCP UL-94V0
SHELL : C2680, NI FINISHED
CONTACT MATERIAL :C5191 GOLD FINISHED

2.ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING : 0.5 AMPS
CONTACT RESISTANCE :20 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 500 V ACMIN.
INSULATION RESISTANCE : 100 MEGAOHMS MIN.

3.MECHANICAL
MATING FORCE:4.5Kgf MAX.
UNMATING FORCE:1.0 Kgf MIN


4.ENVIRONMENTAL
TEMPERATURE RATING : -55°C ~ +105°C




TOLERANCES UNLESS OTHERWISE SPECIFIED		深圳市辉焕科技有限公司			
UNIT (MM)	X. ±0.55	ORIGINAL DATA		TITLE	
	X.X ±0.35	2021-06-27		HDMI A TYPE 母座 直立式H=10.50MM	
	X.XX ±0.25	DWG.		Jack	
	X.XXX ±0.15	CKD.		Larry	
ANGEL ±2°		APPD.		J.L.Y	
3RD.ANGLE'S		PART NO.		SCALE	SIZE
		HDMI-AF002		1:1	A4
		DWG NO.		SHEET	REV.
		HDMI-AF002		1/2	A

RoHS


REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		Jack	Larry	J.L.Y	2022-06-27



- Notes:
- 每卷前空5PCS.后空10PCS, 中间包装300PCS产品, 尾部用美纹胶纸封住, 美纹胶长度为18~20cm.
 - 外圈再卷一圈保护带, 保护带最后重叠50MM MIN. 同样用18~20cm长美纹胶将其封住.
 - 每个卷盘上贴一张物料标签 (按要求填写).
 - 每10卷盘装入1个外箱; 外箱角落用三角板填充. 用透明胶将外箱封口
 - 将标签 (按要求打印好的) 贴在纸箱侧麦上方.
 - 尾数箱用纸壳或其它填充物填满空间, 或将纸箱割小至刚好装下.
 - 在搬运过程中要轻拿轻放.
 - 在运输中不可堆放过多, 不可有重压现象.
- 注: 客户特殊要求请参照业务的出货资料



产品	HDMI 立贴母座	3000
干燥剂	2g	1包
防水袋	750*660*0.05	1个
透明胶	W=45	若干
美纹胶	宽15mm 厚0.08	若干
保护带	透明色	1.2米
下带	32mm透明, T=0.5	10*6.3m
上带 (热封)	25.5mm热封	10*6.3m
卷盘	15~*38mm	10
三角板	双坑B=B 375*360*6	4
纸箱	双坑K=A 390*390*380	1
品名	规格 (mm)	用量 (PCS)



TOLERANCES UNLESS OTHERWISE SPECIFIED					
UNIT	(MM)	ORIGINAL DATA			
X.	±0.55	2022-06-27			
X.X	±0.35	DWG. Jack			
X.XX	±0.25	CKD. Larry			
X.XXX	±0.15	APPD. J.L.Y			
ANGEL	±2'	TITLE			
3RD.ANGLE'S		HDMI AF立贴10.5H卷装图		PART NO.	SCALE
				HDMI-AF002	1:1
				DWG NO.	SIZE
				HDMI-AF002	A4
				SHEET	REV.
				2/2	A