



产品编号 : 1202530273

Product Description : Contrinex Inductive Sensor,
6.5mm Diameter Smooth Housing, 1.5mm Operating
Distance, Embeddable, PNP, NC, 2m 3-wire PVC Cable,
16mm Housing Length

系列号 : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric
Sensors

工程编号 : DW-AD-604-065-120



文件和资源

规格

[1202530270-000.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

合规声明

- EU RoHS
- REACH SVHC
- Low-Halogen

行业文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

关注物质

- PFAS

欧盟 RoHS 合格证书

附加信息

产品详情

一般

状态	Not Recommended For New Design
类别	Inductive Sensors
系列	120253
说明	Contrinex Inductive Sensor, 6.5mm Diameter Smooth Housing, 1.5mm Operating Distance, Embeddable, PNP, NC, 2m 3-wire PVC Cable, 16mm Housing Length
IP 等级	IP67
产品名称	Contrinex
类型	Inductive
UPC	191130064854

电气

输出	NC
极性	PNP
交换频率	≤ 5000 Hz

物理

连接	Cable (PVC 2m, 3-wire)
长度	16mm
材料－外壳	Stainless Steel
材料 – 感应面	PA66
安装方式	Embeddable
工作距离	1.5mm
输出	NC
传感器外壳尺寸	6.5mm dia. (smooth)
运行温度范围	-25° to +70° C