



产品编号 : 1202530076

Product Description : Contrinex Inductive Sensor,
M30 Housing, 40mm Operating Distance, Non-
embeddable, NPN, NO, 2m 3-wire PVC Cable, 60mm
Housing Length

系列号 : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric
Sensors

工程编号 : DW-AD-511-M30



文件和资源

规格

[1202530076-000.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

合规声明

- EU RoHS
- REACH SVHC
- Low-Halogen

行业文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

关注物质

- PFAS

欧盟 RoHS 合格证书

产品详情

一般

状态	Not Recommended For New Design
类别	Inductive Sensors
系列	120253
说明	Contrinex Inductive Sensor, M30 Housing, 40mm Operating Distance, Non-embeddable, NPN, NO, 2m 3-wire PVC Cable, 60mm Housing Length
IP 等级	IP67
产品名称	Contrinex
类型	Inductive
UPC	191130062461

电气

输出	NO
极性	NPN
交换频率	≤ 65 Hz

物理

连接	Cable (PVC 2m, 3-wire)
长度	60mm
材料－外壳	Chrome Plated Brass
材料 – 感应面	PBTP
安装方式	Non-embeddable
工作距离	40mm
输出	NO
传感器外壳尺寸	M30
运行温度范围	-25° to +70° C