






RoHS



TOLERANCE: ± 0.05
RECOMMENDED PCB LAYOUT
(TOP VIEW)

REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		Jack	Larry	J.L.Y	2022-12-2

NOTES

1.ELECTRONIC

CONTACT RESISTANCE: 30mohm MAX
INSULATION RESISTANCE: 100 Mohm MIN
WITHSTAND VOLTAGE:AC 500V,1min.

2.MECHANICAL

DURABILITY: 5000 CYCLE

3. ENVIRONMENT CHARACTERISTICS

OPERATING TEMPERATURE: -55°C TO +105°C

4.RECOMMANDER PCB THICKNESS 1.2




AF238-D xx 1BT x 72HWR

端子电镀要求:	外壳电镀要求:
01: 半金雾锡1U"	E: 外壳镍镍
02: 半金雾锡3U"	G: 外壳镍金
03: 半金雾锡5U"	
04: 半金雾锡10U"	
05: 半金雾锡15U"	
06: 半金雾锡30U"	


3	SHELL	1	STAINLESS STEEL SUS304 T=0.40	NI PLATED		
2	CONTACT	19	COPPER ALLOY C2680 T=0.20	AU/TIN PLATED		
1	HOUSING	1	THERMOPLASTIC	(UL 94V-0) BLACK		
No.	PART NAME	QTY	MATERIAL	REMARK		
TOLERANCES UNLESS OTHERWISE SPECIFIED		深圳市辉煌科技有限公司				
UNIT (MM)						
X. ±0.55	ORIGINAL DATA		TITLE			
X.X ±0.35	2022-12-29		HD AF 沉板3.65MM 外壳厚T=0.40MM DIP L=12.50MM			
X.XX ±0.25	DWG. Jack					
X.XXX ±0.15						
ANGEL ±2°	CKD. Larry		PART NO. HDMI-AF238-CB3.65	SCALE 1:1		
3RD.ANGLE'S		APPD. J.L.Y		SHEET 1/2		
		DWG NO. HDMI-AF238-CB3.65		REV. A		

RoHS

REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW			Jack	Larry	J.L.Y 2023-03-25



W	32.00 ± 0.30	T	0.40 ± 0.05	P ₀	4.00 ± 0.10	A ₀	12.90 ± 0.10
S	28.40 ± 0.10	F	14.20 ± 0.10	P ₂	2.00 ± 0.10	B ₀	19.20 ± 0.10
E	1.75 ± 0.10	P	20.00 ± 0.10	D ₀	$\emptyset 1.50 \pm 0.10$	K ₀	6.30 ± 0.10



		REEL/TRAY	CARTON
CONNECTOR (PCS)		500	4000
TOLERANCES UNLESS OTHERWISE SPECIFIED		深圳市辉煌科技有限公司	
UNIT	(MM)	ORIGINAL DATA 2023-03-25	TITLE HD AF 沉板3.65MM 外壳厚T=0.40MM DIPL=12.50MM (包装图)
X.	± 0.55		
X.X	± 0.35		
X.XX	± 0.25		
X.XXX	± 0.15		
ANGLE	$\pm 2^\circ$		
3RD ANGLE'S		CKD. Larry	PART NO. HDMI-AF238-CB3.65
		APPD. J.L.Y	SCALE 1:1 SIZE A4
		DWG NO. HDMI-AF238-CB3.65	SHEET 2/2 REV. A