



产品编号 : 1202530114

Product Description : Contrinex Inductive Sensor, M18 Housing, 12mm Operating Distance, Quasi-embeddable, PNP, NO, 4-pin M12 Connector, 48.5mm Housing Length

系列号 : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric Sensors

工程编号 : DW-AS-503-M18-120



文件和资源

规格

[1202530108-000.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

合规声明

- EU RoHS
- REACH SVHC
- Low-Halogen

行业文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

关注物质

- PFAS

欧盟 RoHS 合格证书

产品详情

一般

状态	Not Recommended For New Design
类别	Inductive Sensors
系列	120253
说明	Contrinex Inductive Sensor, M18 Housing, 12mm Operating Distance, Quasi-embeddable, PNP, NO, 4-pin M12 Connector, 48.5mm Housing Length
IP 等级	IP67
产品名称	Contrinex
类型	Inductive
UPC	191130062843

电气

输出	NO
极性	PNP
交换频率	≤ 600 Hz

物理

连接	Connector (M12, 4-pin)
长度	48.5mm
材料－外壳	Chrome Plated Brass
材料 – 感应面	PBTP
安装方式	Quasi-embeddable
工作距离	12mm
输出	NO
传感器外壳尺寸	M18
运行温度范围	-25° to +70° C