



产品编号 : 1202530666

Product Description : Contrinex Inductive Sensor,
M30 Fully Stainless Steel, 40mm Operating Distance,
Non-embeddable, NPN, NC, 2m 3-wire TPE Cable,
70.2mm Housing Length

系列号 : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric
Sensors

工程编号 : DW-LD-712-M30



文件和资源

规格

[1202530665-000.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

合规声明

- EU RoHS
- REACH SVHC
- Low-Halogen

行业文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

关注物质

- PFAS

欧盟 RoHS 合格证书

附加信息

产品详情

一般

状态	Not Recommended For New Design
类别	Inductive Sensors
系列	120253
说明	Contrinex Inductive Sensor, M30 Fully Stainless Steel, 40mm Operating Distance, Non- embeddable, NPN, NC, 2m 3-wire TPE Cable, 70.2mm Housing Length
IP 等级	IP68, IP69K
产品名称	Contrinex
类型	Inductive
UPC	191130065967

电气

输出	NC
极性	NPN
交换频率	≤ 90 Hz

物理

连接	Cable (TPE-S 2m, 3-wire)
长度	70.2mm
材料－外壳	Stainless Steel
材料 – 感应面	Stainless Steel
安装方式	Non-embeddable
工作距离	40mm
输出	NC
传感器外壳尺寸	M30
运行温度范围	-25° to +85° C