









版次	内 容	申请人	日期
----	-----	-----	----



PIN	A	B	C
2	7.30	1.50	5.50
3	8.80	3.00	7.00
4	10.30	4.50	8.50
5	11.80	6.00	10.00
6	13.30	7.50	11.50
7	14.80	9.00	13.00
8	16.30	10.50	14.50
9	17.80	12.00	16.00
10	19.30	13.50	17.50
11	20.80	15.00	19.00
12	22.30	16.50	20.50
13	23.80	18.00	22.00
14	25.30	19.50	23.50
15	26.80	21.00	25.00

# 浙江创都电子科技有限公司

产品料号:

1504-WR-S-\*-\*-\*-\*1  
 孔位  
 M1=LCP(自然色)  
 M4=PA9T(自然色)

颜色: 1. 自然色  
 包装: R=卷装  
 电镀: A=亮锡、B=雾锡、C=镀金

MOLEX: 502494

一般公差(TOLERANCE)

X. ± .50 .XX ± .15


.X ± .20 .XXX ± .05

ANGLES ± 1°

产品名称: GH1.5-\*PWT

产品料号:

第一视图

比例 1:1  
单位 mm  
客户

绘图:

审核:

批准:

版次:A01

日期: