

Rohs

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance: 20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance: 800M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)


Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds

(260°C for 10 seconds)



Ordering Information



J	X	XXX	X	XX	X	X	XXXXX	
产品类别 J=黄牛	同层 1=127 2=10 3=10 4=3.66 5=10 6=8.08 7=5.08 A=1.27*2.54	总P数 016=16P	产品名称 1=DIP 2=RA 3=HT 4=SH 5=玻璃纸	电铸厚度 00=常模 01=2μ 02=3μ 03=5μ S=玻璃布	塑胶材料 1=PBT 2=LCP 3=PPS 4=PA6 5=PA6T 9=PA9T	颜色绿色 1=黑色 2=灰色 3=白色 4=蓝色 5=红色 6=黄色 7=其它	包装方式 1=卷装 2=盘装 3=叠装 4=袋装 5=盒装	序号 0001-9999

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		2.8		5.65	5.5
002					

[illegible]