



RoHS

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°c to +105°c



Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V−0)
Standard: PA6T
Max.Processing Temp: 230°C for 30−60 seconds
(260°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXX

产品类别 间距 总Pin数 产品形态 电镀厚度 塑胶材料 塑胶颜色 包装方式 序列号
J=筒子 1=1.27 016=16P 2=DF 00=常规 1=PBT 1=黑色 1=直装 0001-9999
2=2.0 2=2.54 2=RA 2=LCP 2=灰色 2=卷装
3=2.54 3=3.96 3=SM 02=20μ" 3=PPS 3=白色 3=卷装
4=3.96 5=10 5=SM 03=30μ" 4=PA6 4=蓝色 4=段装
5=10 7=5.08 5=SM 05=50μ" 5=PA6T 5=红色 5=段装
7=5.08 A=1.27*2.54 9=PA9T 6=黄色 6=直装
7=灰白色 7=灰白色



Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	10.5		9.5	8.8	8.7
002					

深圳市连盛精密连接器有限公司

				OPERATION		DRAW			SCALE		FIT	深圳市连盛精密连接器有限公司		
				X.X	±0.30				UNIT	mm				
				X.XX	±0.20	CHECK			SIZE	A4				
				X.XXX	±0.10				SHEET	1/1				
A0	2012.03.28	NEW DRAWING		Angle	±3°	APPROVE			PROJ.		TITLE:			
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL									2.54BOX H8.8mm NP SMT
									PART NO.		1030300320			

1030300320

2.54BOX H8.8mm NP SMT