

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass


Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)



Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds

(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

J X XXX X XX X X X XXX

产品类别 1=1.27 2=2.0 3=2.54 4=3.96 5=1.0 6=0.08 7=3.08 A=1.27*2.54
间距 016=16P
产品形态 1=DIP 2=RA 3=SMT 4=SH 5=线绕脚
电镀厚度 00=常规 01=1u" 02=2u" 03=3u" SIK=镀锡
绝缘材料 1=PBT 2=LCP 3=PPS 4=PA46 5=PA6T 9=PA9T
塑胶颜色 1=黑色 2=灰色 3=白色 4=黄色 5=红色 6=灰白色 7=灰白色
包装方式 1=管装 2=卷装 3=盒装 4=袋装 5=盒装
序列号 0001-9999

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		2.8		5.65	5.5
002					

OPERATION		DRAW		SCALE		FIT		PART NO.		TITLE:	
X.X		±0.30		UNIT		mm		A4		1030200143	
X.XX		±0.20		CHECK		SIZE		A4		2.0Box Npin H5.65 180°	
X.XXX		±0.10		APPROVE		SHEET		1/1			
Angle		±3°		PROJ.		PROJ.					
DIM		TOL									

深圳市连盛精密连接器有限公司

1030200143

2.0Box Npin H5.65 180°