

Rohs

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000MΩ Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au or Sn Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PBT

Max.Processing Temp: 180°C for 30-60 seconds

(200°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)

Ordering Information

J	X	XXX	X	XX	XX	X	X	XXXX
产品类型 J=肩片	肩宽 1=27 2=30 3=2.54 4=3.36 5=1.0 6=0.8 7=5.07 A=12/7.2.54	总片数 016=16P	产品种类 1=RA 2=SA 3=SMT 4=SH 5=线钩制	电轴厚度 00= 常流 01=20° 02=20° 03=30° SN=玻璃	塑胶材料 1=FD 2=PPS 3=PA46 5=PA6T 9=PA9T	塑胶颜色 1=黑色 2=灰色 3=白色 4=蓝色 5=红色 6=黄色 7=米白色	包卷方式 1=单卷 2=双卷 3=三卷 4=四卷 5=二投	序列号 0001-9999

[illegible]

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		3,3		8,8	8,7
002					