

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass



Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds



(260°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXXX

产品类别	同层	点焊	产品形状	电镀厚度	塑胶材料	塑胶颜色	包装方式	序列号
产品类别	1=1.27	016=16P	1=DIP	00=常规	1=PBT	1=黑色	1=管接	0001-9999
同层	2=2.0		2=RA	01=1u"	2=LCP	2=灰色	2=直插	
	3=2.54		3=SMT	02=2u"	3=PPS	3=白色	3=直插	
	4=3.96		4=SH	03=3u"	4=PA46	4=黄色	4=波接	
	5=1.0		5=线绕	5=PA6T	5=红色	5=黄色	5=波接	
	6=0.8							
	7=5.08							
	A=1.27~2.54							



Dimension antitheses list

ITEM	PB	PC	PW	H	W
001	6.3		6.9	5.65	5.5
002					

深圳市连盛精密连接器有限公司

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	OPERATION		DRAW	SCALE		FIT	PART NO.	TITLE:	2.0Box Npin H5.65 SMT
							X.X	±0.30		UNIT	mm				
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10	CHECK		±0.20		SIZE	A4		1030200152		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE				SHEET	1/1				