





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40℃ to +105℃

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V−0)
Standard: PBT
Max.Processing Temp: 180°C for 30−60 seconds
(200°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXX

产品类别	间距	总Pin数	产品形态	电镀厚度	塑胶材料	塑胶颜色	包装方式	序列号
J=附件	1=1.27	016=16P	1=DIP	00=常规	1=PBT	1=黑色	1=管装	0001-9999
	2=2.0		2=RA	01=1u"	2=LCP	2=灰色	2=卷装	
	3=2.54		3=SMT	02=2u"	3=PPS	3=白色	3=盒装	
	4=3.0		4=SMT	03=3u"	4=PA46	4=蓝色	4=卷装	
	5=4.0		5=侧插脚	SN=镀锡	5=PA6T	5=红色	5=盒装	
	6=5.08				6=PA6T	6=黄色		
	7=5.08				7=PA9T	7=灰白色		
	A=1.27*2.54							

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		3.0		8.8	8.7
002					

深圳市连盛精密连接器有限公司

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司
				X.X	±0.30				UNIT	mm	
B	2013.08.15	变更产品针长,将原来的L=16.5/21.5改成,L=16.0/21.0	YIYUSHENG	X.XX	±0.20	CHECK		SIZE	A4	PART NO. 1030300101	
A	2012.09.10	NEW DRAWING		X.XXX	±0.10			SHEET	1/1		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	±3'	APPROVE		PROJ.			