



RoHS

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°c to +105°c



Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V−0)
Standard: PA6T
Max.Processing Temp: 230°C for 30−60 seconds
(260°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXXX

产品类别 间距 总Pin数 产品形态 电镀厚度 塑胶材料 塑胶颜色 包装方式 序列号
J=筒子 1=1.27 016=16P 2=DF 00=常规 1=PBT 1=黑色 1=直装
2=2.0 2=2.0 01=1u" 2=LCP 2=灰色 2=卷装
3=2.54 3=2.54 02=2u" 3=PPS 3=白色 3=弯装
4=3.96 4=3.96 03=3u" 4=PA46 4=蓝色 4=弯装
5=5.0 5=5.0 5=5.0 5=PA6T 5=红色 5=直装
6=6.0 6=6.0 6=6.0 6=PA6T 6=黄色 6=直装
7=5.08 7=5.08 7=5.08 7=PA6T 7=白色 7=直装
A=1.27*2.54



Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	10.5		9.5	8.8	8.7
002					

深圳市连盛精密连接器有限公司												
REV	DATE	MODIFICATION	DESCRIPTION	CHANGE	OPERATION		DRAW					
					X.X	±0.30						
					X.XX	±0.20	CHECK					
					X.XXX	±0.10						
A0	2012.03.28		NEW DRAWING		Angle	±3°	APPROVE					
					DIM	TOL						
										SCALE		FIT
										UNIT		mm
										SIZE		A4
										SHEET		1/1
PROJ.												
TITLE:												