

1	2	3	4	5	6	7	8	9
RoHS								

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:−40℃ to +105℃

Contact Material:Brass




Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V−0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30−60 seconds

(260℃ for 10 seconds)



Ordering Information

J X XXX X XX X X X XXXX

产品系列 1=I27 2=20 3=254 4=396 5=10 6=08 7=508 A=I27*254
产品形状 1=DIP 2=RA 3=SMT 4=SH 5=线绕型
电镀厚度 00=常规 01=1u" 02=2u" 03=3u" SMT=线绕
塑胶材料 1=PBT 2=LCP 3=PPS 4=PA46 5=PA6T 9=PA9T
塑胶颜色 1=黑色 2=灰色 3=白色 4=黄色 5=红色 6=黄色 7=灰白色
包装方式 1=管装 2=盘装 3=盒装 4=袋装 5=盒装
序列号 0001-9999

Dimension antitheses list

ITEM	PB	PC	PW	H	W
001	6.3		6.9	5.65	5.5
002					

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		PART NO.		
X.X		±0.30		UNIT		mm		
X.XX		±0.20		CHECK		SIZE A4		
X.XXX		±0.10		APPROVE		SHEET 1/1		
Angle		±3°		PROJ.		TITLE:		
DIM		TOL		PROJ.		2.0Box Npin H5.65 SMT		