



RoHS

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°C to +105°C



Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V−0)
Standard: PA6T
Max.Processing Temp: 230°C for 30−60 seconds
(260°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXX

产品类别 间距 总Pin数 产品形态 电镀厚度 塑胶材料 塑胶颜色 包装方式 序列号
J=筒子 1=1.27 016=16P 2=DF 00=常规 1=PBT 1=黑色 1=直装
2=2.0 2=2.54 01=1u" 2=LCP 2=灰色 2=卷装
3=2.54 4=3.96 02=2u" 3=PPS 3=白色 3=弯装
5=3.0 5=5.0 03=3u" 4=PA46 4=蓝色 4=弯装
7=5.08 5=5.08 5=5.08 5=PA6T 5=红色 5=直装
A=1.27*2.54 6=黄色 6=黄色 7=灰白色 7=灰白色



Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	10.5		9.5	8.8	8.7
002					

				OPERATION		DRAW				SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4			
				X.XXX	±0.10				SHEET	1/1			
A0	2012.03.28	NEW DRAWING		Angle	±3°	APPROVE			PROJ.				
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL						TITLE:	2.54BOX H8.8mm NP SMT	
												PART NO.	1030300321