

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass



Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds



(260°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXXX

产品类别	同层	点焊	产品形状	电镀厚度	塑胶材料	塑胶颜色	包装方式	序列号
1=背牛	1=1.27	016=16P	1=DIP	00=常规	1=PBT	1=黑色	1=管接	0001-9999
2=2.0	2=2.0		2=RA	01=1u"	2=LCP	2=灰色	2=直插	
3=2.54	3=2.54		3=SMT	02=2u"	3=PPS	3=白色	3=直插	
4=3.96	4=3.96		4=SH	03=3u"	4=PA46	4=黄色	4=波接	
5=1.0	5=1.0		5=线绕脚	5=PA6T	5=红色	5=黄色	5=盒接	
6=0.8	6=0.8			9=PA9T	6=白色	7=灰白色		
7=5.08	7=5.08							
A=1.27~2.54	A=1.27~2.54							



Dimension antitheses list

ITEM	PB	PC	PW	H	W
001	6.3		6.9	5.65	5.5
002					

深圳市连盛精密连接器有限公司

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW				SCALE		FIT	深圳市连盛精密连接器有限公司
				X.X	±0.30					UNIT	mm		
				X.XX	±0.20	CHECK				SIZE	A4		
				X.XXX	±0.10					SHEET	1/1		
				Angle	±3°	APPROVE				PROJ.			
				DIM	TOL								