

Rohs

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au or Sn Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PBT

Max.Processing Temp: 180°C for 30-60 seconds

(200°C for 10 seconds)





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

Ordering Information

J	X	XXX	X	XX	X	X	XXXX	
产品类型 J=筒机	筒围 1号=27 2号=32 3号=35.4 4号=3.96 5=1.0 6=0.8 7=5.08 A=1.27-2.54	总门数 016=16P	产品形态 1=RA 2=RA 3=SMT 4=SH 5=线钩网	电筒亮度 00=无光源 01=1W 02=2W 03=3W SM=磁筒	塑胶材料 1=PET 2=PC 3=PE 4=PP 5=PA6 9=PA3T	颜色 1=黑色 2=灰色 3=白色 4=蓝色 5=红色 6=黄色 7=灰白色	包装方式 1=筒装 2=箱装 3=盘装 4=袋装 5=盒装	序列号 0001-9999

深圳市连盛精密连接器有限公司									
		SCALE		FIT		PART NO. 1030300159			
		UNIT		mm					
		SIZE		A4					
		SHEET		1/1		TITLE: 2.54BOX NP H=8.8 DIP PC3.3 L=11.5 AU0.6U PBT 黑色			
		PROJ.							
		OPERATION		DRAW					
		X.X		±0.30					
		X.XX		±0.20					
		X.XXX		±0.10					
		Angle		±3°		APPROVE			
		DIM		TOL					
REV	DATE	MODIFICATION DESCRIPTION		CHANGE					
A0	2012.03.28	NEW DRAWING							



Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		3,3		8,8	8,7
002					

深圳市连盛精密连接器有限公司

PART NO.	1030300159
----------	------------

ТТЛ F.	2.54BOX NP H=8.8 DIP PC3.3
--------	----------------------------

A	B	C	D	E	F	G
---	---	---	---	---	---	---