



RoHS

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°c to +105°c



Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V−0)
Standard: PA6T
Max.Processing Temp: 230°C for 30−60 seconds
(260°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXXX

产品类别 间距 总Pin数 产品形态 电镀厚度 塑胶材料 塑胶颜色 包装方式 序列号
J=筒子 1=1.27 016=16P 2=DF 00=常规 1=PBT 1=黑色 1=直装
2=2.0 2=2.54 01=1u" 2=LCP 2=灰色 2=卷装
3=2.54 3=3.96 02=2u" 3=PPS 3=白色 3=直装
4=3.96 5=5.0 03=3u" 4=PA46 4=蓝色 4=卷装
5=5.0 7=5.08 5=特殊脚 5=PA6T 5=红色 5=直装
6=黄色 7=灰白色



Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	10.5		9.5	8.8	8.7
002					

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30			UNIT	mm		
X.XX	±0.20	CHECK		SIZE	A4		
X.XXX	±0.10			SHEET	1/1		
Angle	±3°	APPROVE		PROJ.			
DIM	TOL						
深圳市连盛精密连接器有限公司							
PART NO.				1030300271			
TITLE:				2.54BOX H8.8mm NP SMT			