

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40°C to +105°C


Contact Material:Brass

Contact Plating:Au or Sn Over Ni


Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

J X XXX X XX X X X XXXX

产品类别 1=127 2=2.0 3=2.54 5=1.8 7=5.08 A=1.27/2.54
总Pin数 016=16P
产品形态 1=01P 2=RA 3=SN 5=板级脚
电镀厚度 00=镀镍 02=2u" 03=3u" SH=镀锡
塑胶材料 1=PB1 2=LCp 3=PPS 4=PA46 5=PA6T 9=PA9T
塑胶颜色 1=黑色 2=灰色 3=白色 4=黄色 5=红色 6=黄色 7=灰白色
包装方式 1=卷装 2=卷装 3=卷装 4=卷装 5=盒装
序列号 0001-9999

				OPERATION		DRAW	SCALE		FIT	深圳市连盛精密连接器有限公司			
				X.X	±0.30		UNIT	mm					
A1	2014.12.26	总高9.2改为9.0		X.XX	±0.20	CHECK	SIZE	A4		PART NO.	1030200095		
A0	2012.07.26	NEW DRAWING		X.XXX	±0.10		SHEET	1/1		TITLE:	2.0Box Header Npin H5.65		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	PROJ.				L=10.5/14.5 90°		
1	2	3	4	5	6	7	8	9					