





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V−0)
Standard: PBT
Max.Processing Temp: 180°C for 30−60 seconds
(200°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

J	X	XXX	X	XX	X	X	X	XXXX
产品类型 J= 筒中	间距 1=1.27 2=2.0 3=2.54 4=3.96 5=1.0 6=1.0 7=5.08 A=1.27*2.54	总Pin数 016=16P	产品形态 1=DIP 2=RA 3=SNIT 5=线绕脚	电镀厚度 00=常规 01=1u" 02=2u" 03=3u" SR=镀锡	绝缘材料 1=PBT 2=ICP 3=PPS 4=PA46 5=PA6T 9=PA9T	绝缘颜色 1=黑色 2=灰色 3=白色 4=蓝色 5=红色 6=黄色 7=灰白色	包装方式 1=卷装 2=散装 3=散装 4=散装 5=散装	序列号 0001-9999

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		3.3		8.8	8.7
002					

深圳市连盛精密连接器有限公司									
				SCALE		FIT		PART NO. 1030300221	
				UNIT		mm			
				SIZE		A4			
				SHEET		1/1			
				PROJ.					
				TITLE:		2.54BOX NP H=8.8 DIP PC3.3 L=11.5 AU0.6U PBT 黑色			