

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass




Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

J X XXX X XX X X X XXXX

产品类别	间距	总Pin数	产品形态	电镀厚度	绝缘材料	塑胶颜色	包装方式	序列号
1=扁平	1=1.27	016=16P	1=DIP	00=常规	1=PBT	1=黄色	1=管接	0001-9999
	2=2.0		2=RA	2=1u"	2=LCP	2=灰色	2=管接	
	3=2.54		3=SMT	3=5u"	3=PPS	3=白色	3=盘接	
	4=3.96		4=SH	03=0.1"	4=PA46	4=黄色	4=盘接	
	5=1.0		5=贴片	5=PA6T	5=红色	5=黄色	5=盘接	
	6=0.08				9=PA9T	6=灰色		
	7=3.08					7=灰白色		
	A=1.27*2.54							

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		2.8		5.65	5.5
002					

深圳市连盛精密连接器有限公司										
OPERATION		DRAW				SCALE		FIT		
		X.X	±0.30			UNIT	mm			
		X.XX <td>±0.20<td>CHECK</td><td></td><td></td><td>SIZE<td>A4</td><td rowspan="4">PART NO. 1030200042</td></td></td>	±0.20 <td>CHECK</td> <td></td> <td></td> <td>SIZE<td>A4</td><td rowspan="4">PART NO. 1030200042</td></td>	CHECK			SIZE <td>A4</td> <td rowspan="4">PART NO. 1030200042</td>	A4	PART NO. 1030200042	
		X.XXX <td>±0.10</td> <td></td> <td></td> <td></td> <td>SHEET</td> <td>1/1</td>	±0.10				SHEET	1/1		
A0	2012.03.28	NEW DRAWING						TITLE:		2.0Box Npin H5.65 180°
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	PROJ.			