

Rohs

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:400V AC/DC

Insulation Resistance: 800M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds

(260°C for 10 seconds)





Ordering Information

XXXXXXXXXXXX

产品类别	产品型号	产品描述	品牌/度	规格/材料	颜色/色	每包/式	序列号
心=黄片	1=1.27	1-DIP	00.146	1-PR1	1=黑	1=1式	001-9999
1=2.20	016=16P	2-R4	00.146	2-LCP	2=灰	2=2式	
2=2.20		3-SMT	02.20*	3=PLP	3=白	3=3式	
4=3.36		4=5H	03.30*	4=PA46	4=灰	4=4式	
5=0.8		5=耐碱		5=PA6T	5=灰	5=5式	
6=0.8		SN=玻璃		9=PA9T	6=黄		
7=5.08					7=灰		
A=1.27/2.54					7=灰		

Dimension antitheses list

ITEM	PB	PC	PW	H	W
001		2.8		5.65	5.5
002					



			OPERATION		DRAW				SCALE		深圳市连盛精密连接器有限公司	
			X.X	±0.30					UNIT	FIT		
			X.XX	±0.20	SIZE	A4	PART NO.	1030200056				
			X.XXX	±0.10					SHEET	1/1		
A0	2012.03.28	NEW DRAWING			APPROVE			TITLE:	2.0Box Npin H5.65 180°			
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	PROJ.						