






NOTES:
MATERIAL
INSULATOR: GLASS FILLED THERMO-PLASTIC. UL 94V-0
CONTACT: COPPER ALLOY
GROUND CONTACT: COPPER ALLOY
GROUND PLATE: COPPER ALLOY
SPECIFICATION
CURRENT RATING: 0.5A
CONTACT RESISTANCE: 50mΩ MAX
INSULATION RESISTANCE: 500MΩ MIN AT 500V DC
OPERATING TEMPERATURE RANGE: -40°C TO +125°C

CODING INFORMATION:
L B B 5 * * - * 2 2 0 S - B 0 R
LXWCONN
PACKING: R: CARRIER REEL
0: 标准样式
B: BLACK
S: SOCKET
PIN
PLATING: G: 1u" Au Min (G/F)
HEIGHT: 74: 7.45 mm
44: 4.45 mm
5: PITCG 0.50
8: 8u" Au Min
E: 30u" Au Min
SERIAL CODE



RECOMMENDED PCB LAYOUT
G: GROUND

FULL-MATING CONDITION

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

RoHS
Compliant
2013/95/EC



修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差 GENERAL TOLERANCE
.X ±0.50
.XX ±0.30
.XXX ±0.10
ANGLES ±1°

制图 (DR): Johnny 2023.04.11	品名 (TITLE): 0.5MM BTB SOCKET 220PIN WITH GROUND PLATE 16Gpb/s
审核 (CHKD):	料号 (PART NO): LBB5**-220S-B0R
核准 (APPD): Tong 2023.04.11	比例 (SCALE): 1:1
	单位 (UNITS): mm
	张数 (SHEET): 1 OF 1
	图幅 (SIZE): A4