

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40°C to +105°C


Contact Material:Brass

Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

Ordering Information

J X XXX X XX X X X XXXX

产品类别 1=127 2=2.0 3=2.54 5=1.27 7=5.08
总Pin数 016=16P
产品形态 1=01P 2=RA 3=SN 5=板级脚
电镀厚度 00=镀镍 02=2u" 03=3u" 9=PA9T
塑胶材料 1=PB1 2=LCp 3=PPS 4=PA46 5=PA6T
塑胶颜色 1=黑色 2=灰色 3=白色 4=黄色 5=红色 6=黄色 7=灰白色
包装方式 1=卷装 2=卷装 3=卷装 4=卷装 5=盒装
序列号 0001-9999

REV	DATE	MODIFICATION DESCRIPTION	OPERATION		DRAW	SCALE		PART NO.	TITLE:
			X.X	±0.30		UNIT	mm		
A1	2014.12.26	总高9.2改为9.0	X.XX	±0.20	CHECK	SIZE	A4	1030200016	2.0Box Header Npin H5.65
A0	2012.07.26	NEW DRAWING	X.XXX	±0.10		SHEET	1/1		L=10.5/14.5 90°
1	2	3	4	5	6	7	8	9	

深圳市连盛精密连接器有限公司