





1	2	3	4	5	6	7	8	9
RoHS								

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40℃ to +105℃

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V−0)
Standard: PBT
Max.Processing Temp: 180°C for 30−60 seconds
(200°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXX

产品类别 1=127 2=2.0 3=2.54 4=5.08 5=1.0 6=0.8 7=5.08 A=1.27*2.54
总Pin数 016=16P
产品形态 1=DIP 2=RA 3=SOIT 5=线绕脚
电镀厚度 00=常規 01=1u" 02=2u" 03=3u" 4=PA46 5=PA6T 9=PA9T
塑胶材料 1=PBT 2=LCP 3=PPS 4=PA46 5=PA6T 6=黄色 7=灰白色
塑胶颜色 1=黑色 2=灰色 3=白色 4=蓝色 5=红色 6=黄色 7=灰白色
包装方式 1=管装 2=卷装 3=盒装 4=散装 5=盒装
序列号 0001-9999

深圳市连盛精密连接器有限公司									
PART NO.		1030300328							
TITLE:		2.54BOX NP H=8.8 正弯 PC3.0							
PROJ.		SCALE		FIT					
		UNIT		mm					
		SIZE		A4					
		SHEET		1/1					
		Angle		±3°					
		DIM		TOL					
		CHANGE							
		MODIFICATION DESCRIPTION							
		DATE							
		REV							
		A		2012.09.10					
		B		2013.08.15		变更产品针长,将原来的L=16.5/21.5改成,L=16.0/21.0			
						YIYUSHENG			
						DRAW			
						CHECK			
						APPROVE			