

Rohs

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass


Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)




Standard: PBT

Max.Processing Temp: 180°C for 30–60 seconds

(200°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



Ordering Information

2 X XXX X X X XXX

产品类别	间距	总Pin数	产品形态	电镀厚度	塑胶材料	塑胶颜色	包装方式	序列号
J=筒牛	1=1.27 2=2.00	016=16P	1=DIP 2=PLCC	00=常规 1=厚板	1=PBT	1=黑色	1=管装	0001-9999

3=2.54
 4=3.86
 5=1.0
 6=0.8
 7=5.08
 A=1.27x2.54
 0=10"
 3=SMT
 4=SH
 5=鍍硬金
 00=2u"
 00=3u"
 5=鍍硬金
 2=LP
 3=PPS
 5=白色
 4=PA6
 5=PA6T
 9=PA9T
 2=灰色
 3=白色
 4=藍色
 5=紅色
 6=黃色
 7=灰白色

			OPERATION		DRAW							深圳市连盛精密连接器有限公司
			X.X	±0.30								
B	2013.08.15	变更产品针长,将原来的L=16.5/21.5改成,L=16.0/21.0	X.XX		CHECK							
A	2012.09.10	NEW DRAWING	X.XXX	±0.10								
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE						
												PART NO. 1030300085
												TITLE: 2.54BOX NP H=8.8 正弯 PC3.0

深圳市连盛精密连接器有限公司

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001		3,0		8,8	8,7
002					