

# ROHS

## SPECIFICATIONS

Rated Current: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C

Contact Material: Brass



Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max. Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)



Recommended P.C.B Layout (Top Side)  
 (PCB BOARD TOLERANCE ±0.05)



## Ordering Information

J X XXX X XX X X X XXXX

产品类别	间距	插孔数	产品形态	电镀厚度	塑胶材料	塑胶颜色	包装方式	序列号
J=扁平	1=1.27 2=2.0 3=2.54 4=3.96 5=5.0 7=5.08 A=1.27*2.54	016=16P	1=DF 2=RF 3=SM 5=贴片	00=常规 01=1u" 02=2u" 03=3u" 9=PA6T	1=PBT 2=LCP 3=PPS 4=PA46 9=PA9T	1=黑色 2=灰色 3=白色 4=蓝色 5=红色 6=黄色 7=灰白色	1=管装 2=卷装 3=袋装 4=散装 5=盘装	0001-9999



Dimension antitheses list

ITEM	PB	PC	PW	H	W
001	10.5		9.5	8.8	8.7
002					

深圳市连盛精密连接器有限公司

PART NO. 1030300275

TITLE: 2.54BOX H8.8mm NP SMT

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	SCALE		FIT	
				X.X	±0.30		UNIT	mm		
A0	2012.03.28	NEW DRAWING		X.XX	±0.20	CHECK	SIZE	A4	SHEET	1/1
1	2	3	4	5	6	7	8	9		