







X	
PART NO	vigor
2	G2
3	G3
4	G4
5	G5
6	G6
7	G7
8	G8
9	G9
10	G10



Circuit Diagram



- Specification:
- 1.Rating: DC 30V 50mA
 - 2.Travel: 2.5±0.1mm
 - 3.Operating Force:A-B 200gf±75gf
B-A 200gf±75gf
 - 4.Contact Resistance:100mΩ Max
 - 5.Life:10,000 Cycles Min

X=3mm

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE	ITEM			
⑥	Contact	1	Phosphor Bronze	Ag Plated		
⑤	Spring	1	Steel Wire	Temper		
④	Terminal	3	Brass Strip	Ag Plated		
③	Base	1	Phenolic Resin	Natural		
②	Frame	1	Spcc	Black		
①	Knob	1	POM	Black		
ITEM	PART NAME	QTY.	MATERIAL	FINISHING		

APPROVALS	DATE	DRAWING NO.			
DRAWN	G.M.Chen	2014/11/11	SS-12F33-GX		
CHECKED			VERTICAL SLIDE SWITCHES		
APPROVALS			DEALON ELECTRONICS CO.,LTD		

TOLERANCES ARE		ANGLE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
30±0.1	±0.30	±2°			
10±0.10	±0.20				
5±0.10	±0.15				