

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:-40°C to +105°C


Contact Material:Brass

Contact Plating:Au or Sn Over Ni


Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

J X XXX X XX X X X XXXX

产品类别 1=127 2=2.0 3=2.54 5=1.27 7=5.08
总Pin数 016=16P
产品形态 1=01P 2=RA 3=SN 4=SN 5=板级脚
电镀厚度 00=镀镍 01=1μ" 02=2μ" 03=3μ" 9=PA9T
塑胶材料 1=PB1 2=LCp 3=PPS 4=PA46 5=PA6T
塑胶颜色 1=黑色 2=灰色 3=白色 4=黄色 5=红色 6=黄色 7=灰白色
包装方式 1=卷装 2=卷装 3=卷装 4=卷装 5=盒装
序列号 0001-9999

Dimension antitheses list

ITEM	PB	PC	PW	H	W
001	9.0	2.7	5.65	5.5	
002					

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X		±0.30		UNIT		mm		1030200130	
X.XX		±0.20		CHECK		SIZE		A4	
X.XXX		±0.10		SHEET		1/1		2.0Box Header Npin H5.65	
Angle		±3°		APPROVE		PROJ.		TITLE:	
DIM		TOL		CHANGE		L=10.5/14.5 90°			