



RoHS

SPECIFICATIONS

Rated Current:3.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:1000V AC/DC  
Insulation Resistance:1000MΩ Min  
Operation Temperature:-40°C to +105°C

Contact Material:Brass  
Contact Plating:Au Over Ni  
Insulator Material:Polyester(UL94V-0)  
Standard: PA6T  
Max.Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)





Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)

Ordering Information

J X XXX X XX X X X XXXX

产品类别 间距 总Pin数 产品形态 电镀厚度 塑胶材料 塑胶颜色 包装方式 序列号  
J=筒子 1=1.27 016=16P 2=DF 00=常规 1=PBT 1=黑色 1=直装 0001-9999  
2=2.0 2=2.54 2=RA 2=LCP 2=灰色 2=卷装  
3=2.54 3=3.96 3=SM 3=PPS 3=白色 3=卷装  
4=3.96 5=1.0 5=SM 5=PA46 4=蓝色 4=卷装  
5=1.0 7=5.08 5=PA6T 5=红色 5=直装  
A=1.27\*2.54 6=黄色 7=灰白色



| Dimension antitheses list |      |    |     |     |     |
|---------------------------|------|----|-----|-----|-----|
| ITEM                      | PB   | PC | PW  | H   | W   |
| 001                       | 10.5 |    | 9.5 | 8.8 | 8.7 |
| 002                       |      |    |     |     |     |

深圳市连盛精密连接器有限公司

| REV | DATE       | MODIFICATION DESCRIPTION | CHANGE | OPERATION |       | DRAW    | SCALE |    | FIT | PART NO.   | TITLE:                |
|-----|------------|--------------------------|--------|-----------|-------|---------|-------|----|-----|------------|-----------------------|
|     |            |                          |        | DIM       | TOL   | APPROVE | UNIT  | mm |     |            |                       |
| A0  | 2012.03.28 | NEW DRAWING              |        | X.XX      | ±0.10 | CHECK   | SIZE  | A4 |     | 1030300162 | 2.54BOX H8.8mm NP SMT |
| 1   | 2          | 3                        | 4      | 5         | 6     | 7       | 8     | 9  |     |            |                       |