

Rohs

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:400V AC/DC

Insulation Resistance: 800M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds

(260°C for 10 seconds)





Ordering Information

XXXXXXXXXXXX

产品类别	产品型号	产地/厂家	产品用途	中德互译	塑料材料	颜色/着色	包装形式	序列号
1=黄件	1=127	1=德国	1=DPE	00=黄件	1=PB1	1=黄绿色	1=单块式	0001-9999
2=2,0	2=2,0	2=美国	2=RA	01=2"u"	2=CP	2=灰色	2=连续式	
3=3,54	3=3,54	3=美国	3=SAT	02=2"u"	3=PPS	3=白色	3=连续式	
5=5,06	5=5,06	5=美国	5=SE	03=3"u"	4=PA46	4=蓝色	4=连续式	
6=0,8	6=0,8	6=美国	5=玻璃	SH=玻璃	5=PA67	5=红色	5=连续式	
7=5,08	7=5,08	7=美国			9=PA97	6=黄色		
A=127x5,4						7=灰白色		

Dimension antitheses list

ITEM	PB	PC	PW	H	W
001		2.8		5.65	5.5
002					



				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30							
				X.XX	±0.20							
				X.XXX	±0.10							
A0	2012.03.28	NEW DRAWING		Angle	±3°	CHECK			SIZE	A4	PART NO.	1030200051
				DIM	TOL	APPROVE			SHEET	1/1		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE						PROJ.		TITLE:	2.0Box Npin H5.65 180°

深圳市连盛精密连接器有限公司

T NO.	1030200051
-------	------------

E:	2.0Box	Np'in	H5.65	180°
----	--------	-------	-------	------