

1	2	3	4	5	6	7	8	9
RoHS								

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:400V AC/DC

Insulation Resistance:800MΩ Min

Operation Temperature:−40°c to +105°c

Contact Material:Brass



Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V−0)

Standard: PA6T

Max.Processing Temp: 230°C for 30−60 seconds



(260°C for 10 seconds)



Ordering Information

J X XXX X XX X X X XXXX

产品类别 1=1.27 2=2.0 3=2.54 4=3.96 5=1.0 6=0.08 7=5.08 A=1.27*2.54
产品形状 1=DIP 2=RA 3=SMT 4=SH 5=线绕型
电镀厚度 00=常规 01=1u" 02=2u" 03=3u" SMT=线绕
塑胶材料 1=PBT 2=LCP 3=PPS 4=PA46 5=PA6T 9=PA9T
塑胶颜色 1=黑色 2=灰色 3=白色 4=黄色 5=红色 6=黄色 7=灰白色
包装方式 1=管装 2=盘装 3=盘装 4=盘装 5=盘装
序列号 0001-9999



Dimension antitheses list

ITEM	PB	PC	PW	H	W
001	6.3		6.9	5.65	5.5
002					

深圳市连盛精密连接器有限公司

深圳市连盛精密连接器有限公司									
OPERATION		DRAW		SCALE		FIT		PART NO. 1030200149	
				UNIT		mm			
				SIZE		A4			
				SHEET		1/1			
REV	DATE	MODIFICATION	DESCRIPTION	CHANGE	DIM	TOL	APPROVE	PROJ.	TITLE: 2.0Box Npin H5.65 SMT
A0	2012.03.28	NEW DRAWING			X.XXX	±0.10			
					Angle	±3°			
					X.XX	±0.20	CHECK		
					X.X	±0.30			