






修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	WANG	2017-07-10




TYPE 1



TYPE 2





TYPE 3



Ordering Information:
HDGC2001WV-XP - ** - **
1 2 3

- 1.Part No.
2.Style:
(blank) -Type 1
2 -Type 2
3 -Type 3
3.Color:
(blank) -White
GN -Green
RD -Red



Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	2.00	6.00	12P	22.00	26.00
3P	4.00	8.00	13P	24.00	28.00
4P	6.00	10.00	14P	26.00	30.00
5P	8.00	12.00	15P	28.00	32.00
6P	10.00	14.00	16P	30.00	34.00
7P	12.00	16.00	17P	32.00	36.00
8P	14.00	18.00	18P	34.00	38.00
9P	16.00	20.00	19P	36.00	40.00
10P	18.00	22.00	20P	38.00	42.00
11P	20.00	24.00			

SPECIFICATIONS:

Current Rating: 2A AC,DC
Voltage Rating:100V AC,DC
Temperature Range: -25°C ~ +85°C
Contact Resistance: 10mΩ Max.
Insulation Resistance: 1000MΩ Min.
Withstanding Voltage: 800V AC/minute
Pin Material: Brass/Tin over Nickel
Material: Nylon 66,UL94V-0(White)



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

TEL : 0755-27111216 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表					TITLE: 产品名称：20010WS-NN				
X.X	±0.30	X.X°	±3°	APPD: 核准：	XIE	PART NO: 产品编号：20010WS-NN-HDGC2001			
X.XX	±0.30	X.XX°	±2°	CHECK: 校对：	WANG	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图：	WANG	2017-07-10	5:1	mm	A008