



REV.	ECN. #	DESCRIPTION	DATE
AO	_____	NEW RELEASE	10/29/21

TOLERANCE: ± 0.05

1. TOUCH AREA OF CONTACT
TIPS NO ELECTRICAL FUNCTION
2.NO FIRST PCB_LAYOUT
CIRCUITS IN THE AREA

1. Material:
 - Housing: High Temperature Thermoplastic
 - Terminal: Copper Alloy
 - Shell: Stainless Steel
2. Plating:
 - Terminal: 50u" Ni Underplated Overall
 - 1u" Au Plated On Contact Area And Solder Area
 - Shell: 50u" Ni Underplated Overall
3. Technical Speciality:
 - Rated Voltage: 30V
 - Current Rating: 0.5A
 - Insulation Resistance: 1000M Ω Min.
 - Contact Resistance: 100m Ω Max.
 - Withstanding Voltage: 500V DC For 1 Minutes.
 - Operating Temperature: -40 $^{\circ}$ C ~ +75 $^{\circ}$ C Humidity 80% R.H Max.

PIIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O

MILLIMETERS	INCH
X. ° ±2°	X. ° ±2°
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX±0.10	.XXX±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBaiLai Metal Plastic Technology Co., Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBaiLaiMetal Plastic Technology Co.,Ltd	




东莞市金比莱五金塑胶科技有限公司

DongGuan JinBiLai Metal Plastic Technology Co.,Ltd

TITLE	1. 13H NO-PUSH NANO-SIM CARD				DR		
PART NUM.	102315213				CHKD		
PRO J.	PAGE	1/2	UNITS	mm	APPD		
	SIZE	A4	SCALE	5:1	DIS NO.	NS008-100<客户图>	


Direction of use →



Carrier Tape

Direction of use →


DETAIL B



DETAIL B

NOTES:

- 1、Packing quantity per plate: 2000PCS/Plate
- 2、Loading and packing method



- 3、Total packaging: 20000PCS/Box

The bottom and top of the carton
Pad it with a piece of pearl cotton

BOX

350*350*340mm

10-REEL

packaging tape

label

Part Number	Description	Quantity
303020176	Carrier band (Lucent , PET W=24 PH=16,T=0.3)	326.4m
303040009	Box (K=K,T=7.0,350*350*340)	1PCS
303060001	PE Bag (T=0.08mm , 730*760*730)	1PCS
303070024	Self-adhesive (W=21.30)	329.4m
303110001	Beam (K=K , T=7.0,95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180017	REEL (BLUE , 13Inches*24mm , ϕ330)	10PCS
102315213	1.13H No-Push Nano-Sim Card	20000PCS

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd					
X. ° ±2°	X. ° ±2°						
.X ±0.30	.X ±0.012						
.XX ±0.20	.XX ±0.008						
.XXX ±0.10	.XXX ±0.004						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLaiMetal Plastic Technology Co.,Ltd		TITLE		1.13H No-Push Nano-Sim Card		DR	
		PART NUM.		102315213		CHKD	
		PRO J.	PAGE	2/2	UNITS	mm	APPD
		SIZE	A4	SCALE	3:2	DIS NO.	NS008-100<客户图>