





NOTES:
1.MATERIAL:
CAGE: COPPER ALLOY, Ni PLATED
THICKNESS 0.25mm
2.PACKAGING: TRAY PACKAGING
3.TEMPERATURE RANGE: -55°C TO +85°C





TITLE SFP28 1X1 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd			
PART NO. SFP28 AG202N1Y00101-1X1Y			GENERAL TOLERANCE		UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:1/3
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°		
			.XXX±0.10			
					REV:A	



NOTES:

- 1. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 2. PADS AND VIAS ARE CHASSIS GROUND, 11 PLACES
- 3. THRU HOLES, PLATING OPTIONAL


TITLE SFP28 1X1 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 AG202N1Y00101-1X1Y			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:2/3
			.XXX±0.10		REV:A



SECTION A-A

RECOMMENDED BEZEL DESIGN

NOTES:
△ MINIMUM PITCH ILLUSTRATED, ENGLISH
DIMENSIONS ARE FOR REFERENCE ONLY

TITLE SFP28 1X1 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. SFP28 AG202N1Y00101-1X1Y			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:3/3	REV:A
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°			
			.XXX±0.10				