

RoHS

1

2





3

4

RECOMMENDED PCB LAYOUT

NAME DATE

DRAWING NUMBER AND DATE		REV.	ECN.#	DESCRIPTION	NAME	DATE
		A0	—	NEW RELEASE	GuoXuetong	10/19/17



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05

■ SET SOLDER AREA
■ COPPER RESTRICTED AREA
1. TOUCH AREA OR CONTACT
TIPS NO ELECTRICAL FUNCTION
2. NO FIRST PCB LAYOUT

CIRCUITS IN THE AREA

PIN/NO	ASSIGNMENT	MULTIMETERS	INSM
C1	VCC	I ⁺ ±2 [°]	I ⁺ ±2 [°]
C2	RST	I ⁻ ±0.30	I ⁻ ±0.002
C3	CLK	.IX ±0.10	.IXI ±0.004
CD	Detec Switch	THE INDICATOR AND INDICATION ARE THE PROPERTY OF JINBILAI METAL PLASTIC TECHNOLOGY CO., LTD DO NOT COPY IT OR LEAK IT TO OTHERS, EXCEPT THE TECHNICAL SUPPORT OF JINBILAI METAL PLASTIC TECHNOLOGY CO., LTD	
C5	GND	PART NO.	102312402
C6	VPP	PRO J. PAGE	12 UNITS/mm APPD
C7	I/O	SIZE	A4 DIS. mm
		SCALE	1:1 DIS. NO. NS002-100<客户图>



东莞市金比来五金塑胶科技有限公司
DongGuan JinBilai Metal Plastic Technology Co., Ltd
JINBILAI

1	2	3	4	5	6	7
E	D	C	B	A		

ROHS

1

2

3

4

5


6

7


Direction of use

NOTES:

- 1、Packing quantity per plate: 1500PCS/Plate
- 2、Loading and packing method



3、Total packaging:15000PCS/Box



Part Number	Description	Quantity
303020071	Carrier band (Iucent , PET W=24 PH=16,T=0.3)	244.8m
303040009	Box (K=K,T=7.0,350*350*340)	1PCS
303060001	PE Bag (T=0.08mm, 730*60*730)	1PCS
303070024	Self-adhesive (W=21.30)	247.8m
303110001	Beam (K=K , T=7.0,95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180017	REEL (BLUE , 13Inches*24mm , φ330)	10PCS
102012402	1.37H Push-Push Nano-Sim Card<NS002-100>	15000PCS

1	2	3	4	5	6	7
E	D	C	B	A		

MULTIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司
I° ±2°	I° ±2°	
.I ±0.30	.I ±0.02	DongGuan JinBilei Metal Plastic TechnologyCo., Ltd
.IX ±0.20	.IX ±0.008	
.XII ±0.10	.XII ±0.004	
TITLE L320 Push-Push Nano-SIM卡		
DR		
PART NUM 102312402		
CNCD		
PRO J. PAGE 2/2 UNIT:mm		
APPD		
SIZE A4 SCALE 1:1 DTS NO. NS002-100<客户图>		

E

D

C

B

A