




CRICUIT DIAGRAM FOR CARD DETECT SWITCH

CARD DETECT SWITCH (CD)

GND

NORMAL.....SHORT
INSERTING CARD.....OPEN

REV.	ECN. #	DESCRIPTION	NAME	DATE
A0	_____	NEW RELEASE	GuoXue tong	12/19/20



RECOMMENDED PCB LAYOUT

TOLERANCE: ± 0.05 

 SMT SOLDER AREA

 COPPER RESTRICTED AREA

1. TOUCH AREA OF CONTACT

TIPS NO ELECTRICAL FUNCTION

2. NO FIRST PCB LAYOUT

CIRCUITS IN THE AREA

1000

1.Material:
Housing: High Temperature Thermoplastic
Terminal: Copper Alloy
Shell: Stainless Steel

2. Plating:
Terminal: 50u" Ni Underplated Overall
G/F Plated On Contact Area
G/F Plated On Solder Area
Sheet: 30u" Ni Underplated Overall
G/F Plated On Solder Area

3. Technical Specification:
Rated Voltage: 30V
Current Rating: 0.5A
Insulation Resistance: 1000MΩ Min.
Contact Resistance: 100mΩ Max.
Withstanding Voltage: 500V DC For 1 Minutes.
Operating Temperature: -40℃~+75℃ Humidity 80% R.H Max.


卡片尺寸
1 : 2

		MILLIMETERS	INCH
PIN/NO	ASSIGNMENT	X. ° ±2°	X. ° ±2°
C1	VCC	.X ±0.30	.X ±0.012
C2	RST	.XX ±0.20	.XX ±0.008
C3	CLK	.XXX ±0.10	.XXX ±0.004
C5	GND	THESE DRAWINGS AND SPECIFICATIONS ARE	
C6	VPP	THE PROPERTY OF Dongguan JinBilai	
C7	I/O	Metal Plastic Technology Co., Ltd	
CD	Detect Switch	COPIED OR USED IN ANY MANNER WITHOUT THE	
		PRIOR WRITTEN CONSENT OF Dongguan	
		JinBilai Metal Plastic Technology Co.,Ltd	

 东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd					
TITLE		1.37H Push-Push Nano-SIM卡座		DR	
PART NO.	102314442-Z			CHKD	
PRO J.	PAGE	1/2	UNITS	mm	APPD
	SIZE	A4	SCALE	1:1	DIS NO.
		NS005-01Z<客户图>			

ROHS


Direction of use





NOTES:

1、Packing quantity per plate: 1500PCS/Plate

2、Loading and packing method



3、Total packaging: 15000PCS/Box



Part Number	Description	Quantity
303020071	Carrier band (Lucent, PET W=24 PH=16,T=0.3)	244.8m
303040009	Box (K=K,T=7.0,350*350*340)	1PCS
303060001	PE Bag (T=0.08mm, 730*760*730)	1PCS
303070024	Self-adhesive (W=21.30)	247.8m
303110001	Beam (K=K, T=7.0,95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180017	REEL (BLUE, 13Inches*24mm, $\phi 330$)	10PCS
102314442-Z	1.37H Push-Push Micro-Sim Card<NS005-010>	15000PCS

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司			
X. ° $\pm 2^\circ$	X. ° $\pm 2^\circ$	DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd			
.X ± 0.30	.X ± 0.012	TITLE	1.37H Push-Push Nano-SIM卡座	DR	
.XX ± 0.20	.XX ± 0.008	PART NUM.	102314442-Z	CHKD	
.XXX ± 0.10	.XXX ± 0.004	PRO J.	PAGE 2/2	UNITS mm	APPD
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		SIZE	A4	SCALE 1:1	DIS NO. NS005-01Z<客户图>